

## YAGB4CLTC516FXOEM

by Burndy  
Catalog ID: YAGB4CLTC516FXOEM

Cu Tubing Hylug, #4 AWG, 5/16 IN Stud



### Product Details

#### General

Application	Power Connector
Connector Type	Terminal
Physical Attribute - Number of Holes	1
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810547656
UPC 12 Digit	7818105476566

#### Dimensions

Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.45 in
Dimension - Pad Width inch	0.61 in
Dimension - Stud Size inch	5/16 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper Str Size	4 AWG
Conductor Type	CU C Str-Size

#### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)