

# YAGB4CLTC516FX

by Burndy  
Catalog ID: YAGB4CLTC516FX

1 Hole HYLUG Cu Battery Terminal, #4 AWG, 5/16" stud, 1.97" L, 0.75" W, Gray



## Product Details

### General

Application	Power Connector
Color Code	Gray
Connector Type	Terminal
Die Index	6
Physical Attribute - Number of Holes	1
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562741
UPC 12 Digit	7818105627411

### Dimensions

Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size inch	5/16 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Str Size	4 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	200 EA
Minimum Pack Quantity	20

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)