



YAGB6CLTC38FX

by Burndy
Catalog ID: YAGB6CLTC38FX

1 Hole HYLUG™ Cu Battery Terminal, 6 AWG, 3/8" stud, 1.61" L, 0.60" W, Blue

Product Details

General

Application	Power Connector
Color Code	Blue
Connector Type	Terminal
Die Index	7
Physical Attribute - Number of Holes	1
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562703
UPC 12 Digit	7818105627033

Dimensions

Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.61 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	7/8 in
Dimension - Stud Size inch	3/8 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Str Size	6 AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200 EA
Minimum Pack Quantity	20

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)