

# YAGB6CLTC516FXOEM

by Burndy  
Catalog ID: YAGB6CLTC516FXOEM

Cu Battery Terminal Lug Type, #6 AWG, Blue, 7 Index, 5/16 IN Stud, 7/8 IN Strip Length



## Product Details

### General

Application	Power Connector
Connector Type	Terminal
Physical Attribute - Number of Holes	1
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810563076
UPC 12 Digit	7818105630766

### Dimensions

Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.61 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	7/8 in
Dimension - Stud Size inch	5/16 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)