

YAK29A2G2

by Burndy
Catalog ID: YAK29A2G2

Prop 65 Notice

Cast Al Straight Stacking Lug, 2-NEMA Holes, 250 kcmil, 0.56" Hole Dia



Product Details

General

Connector Type	Terminal
Die Index	299;705
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810186954
UPC 12 Digit	7818101869544

Dimensions

Dimension - B Length inch	1.91 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.84 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.11 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	250 kcmil
Conductor - AL Str Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)