



YAK2CA2G2

by Burndy
Catalog ID: YAK2CA2G2

Prop 65 Notice

Aluminum Stacking compression terminal, 2 Str., 5.62 IN L, Up to eight conductors can be stacked on one 4 hole pad

Product Details

General

Die Index	K-5/8;BG;243
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810081716
UPC 12 Digit	7818100817166

Dimensions

Dimension - B Length inch	1.1 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.62 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-3/16 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG

Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)