



YAK361A2G1

by Burndy
Catalog ID: YAK361A2G1

Prop 65 Notice

Aluminum Stacking compression terminal, 600 Kcmil, 8.22 IN L, Up to eight conductors can be stacked on one 4 hole pad

Product Details

General

Connector Type	Terminal
Die Index	608;722;786
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810081723
UPC 12 Digit	7818100817233

Dimensions

Dimension - B Length inch	2.65 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	209 mm
Dimension - Length Overall inch	8.22 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-11/16 in

Physical Attribute - Tongue Angle	Offset
-----------------------------------	--------

Conductor Related

Conductor - AL Str Size	600 kcmil
Conductor - AL Str Size Range	600 kcmil
Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)