

YAK39A2G2

by Burndy
Catalog ID: YAK39A2G2

Prop 65 Notice

Al Stacking Terminal Lug, 750 kcmil(Al), 1.75" Spacing.

Features: Compression Terminal, Conductor Type: Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U608, U786 Die, Y45 Tool, U608, U786 Die With PT-6515 Adapter, S786, S722 Die, Y46 Tool, U608, U786 Die With PUADP-1 Adapter, P786, P722 Die, Tongue Angle: Straight, Die Index: 722 Or 608 Or 786



Product Details

General

Application	For Aluminum
Connector Type	Terminal
Die Index	608;722;786
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Sub Brand	HYLUG,TERMINALS
Trade Name	HYLUG™
Type	YAK-A-2G, Stacking Lug
UPC	781810187357
UPC 12 Digit	7818101873577

Dimensions

Dimension - B Length inch	2.65 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	209 mm
Dimension - Length Overall inch	8.22 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-3/4 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	750 kcmil
Conductor - AL Str Size Range	750 kcmil
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)