

# YAK44A2NG8

by Burndy  
Catalog ID: YAK44A2NG8

Prop 65 Notice

Cast Al Terminal Offset Lug, Stacking Hylug, 2 Holes, 1000 kcmil, 302 Index, 0.56" Hole Dia



## Product Details

### General

Die Index	302
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810187555
UPC 12 Digit	7818101875555

### Dimensions

Dimension - B Length inch	2.97 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.18 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	226 mm
Dimension - Length Overall inch	8.88 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	1.62 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - AL Str Size	1000 kcmil
Conductor - AL Str Size Range	1000 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)