

# YAL30T12B

by Burndy  
Catalog ID: YAL30T12B

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 300 kcmil, 1/2" Stud, Short Barrel, Belled End, Tin Plated



## Product Details

### General

Color Code	White
Connector Type	Terminal
Die Index	17
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417225

### Dimensions

Dimension - B Length fraction	1-1/25 in
Dimension - B Length inch	1.04 in
Dimension - Bolt Hole Size inch	0.53 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.82 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1-1/8 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Conductor - Material	Copper
----------------------	--------

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)