

YAL312N

by Burndy
Catalog ID: YAL312N

Prop 65 Notice

Copper HYLUGTM , 2 Hole w/ Inspection Window,350 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing,18 index,Red, Short Barrel, Tin Plated



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417249

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.96 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.00 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.36 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.63 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)