

# YAL322T38

by Burndy  
Catalog ID: YAL322T38

Prop 65 Notice

Copper HYLUGTM , 2 Hole w/ Inspection Window,400 kcmil, 3/8" Stud, 1" Stud Hole Spacing,19 index,Blue, Short Barrel, Tin Plated



## Product Details

### General

Color Code	Blue
Connector Type	Terminal
Die Index	19
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417300

### Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.07 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.80 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.24 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)