



## YAL4CT10

by Burndy  
Catalog ID: YAL4CT10

Prop 65 Notice

Copper HYLUG™, Single Hole w/ Inspection Window, 4 AWG, #10 Stud, 8 index, Gray, Short Barrel, Electro- Tin Plated

### Product Details

#### General

Color Code	Gray
Connector Type	Terminal
Die Index	8
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417515

#### Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - D inch	0.47 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.58 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.51 in
Dimension - Stud Size inch	#10
Physical Attribute - Tongue Angle	Straight

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)