

YAL6CT10

by Burndy
Catalog ID: YAL6CT10

Prop 65 Notice

Copper HYLUG™, Single Hole w/ Inspection Window, 6 AWG, #10 Stud, 7 index, Blue, Short Barrel, Electro- Tin Plated



Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	7
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417577

Dimensions

Dimension - B Length inch	0.54 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - D inch	0.48 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.27 in
Dimension - N inch	0.22 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.41 in
Dimension - Stud Size inch	#10
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)