

YAL8CT516

by Burndy
Catalog ID: YAL8CT516

Prop 65 Notice

Copper HYLUG™, Single Hole w/ Inspection Window, 8 AWG, 5/16" Stud, 49 index, Red, Short Barrel, Electro- Tin Plated



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	6
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417669

Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	0.66 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.52 in
Dimension - Stud Size inch	5/16
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)