

## YALB120F2M8

by Burndy  
Catalog ID: YALB120F2M8

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 120 mm, M8 Stud, 44.5 mm Spacing, Long Barrel, 43 mm Wire Strip Length



### Product Details

#### General

Die Index	15
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810642603
UPC 12 Digit	7818106426033

#### Dimensions

Dimension - B Length inch	1.62 in
Dimension - Hole Size mm	8.4 mm
Dimension - L Length Overall mm	118.6 mm
Dimension - Length Overall inch	4.67 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1.69 in
Dimension - Z inch	0.36 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

10
----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)