

YALB120FM20

by Burndy
Catalog ID: YALB120FM20

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 120 mm, M20 Stud, Long Barrel, 43 mm Wire Strip Length



Product Details

General

Die Index	15
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641767
UPC 12 Digit	7818106417677

Dimensions

Dimension - B Length inch	1.62 in
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	101 mm
Dimension - Length Overall inch	3.98 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1.69 in
Dimension - Z inch	0.89 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)