

## YALB1852M12

by Burndy  
Catalog ID: YALB1852M12

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 185 mm, M12 Stud, 44.5 mm Spacing, Long Barrel, 52 mm Wire Strip Length



### Product Details

#### General

Die Index	18
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639740
UPC 12 Digit	7818106397400

#### Dimensions

Dimension - B Length inch	2.00 in
Dimension - Hole Size mm	13.3 mm
Dimension - L Length Overall mm	139.2 mm
Dimension - Length Overall inch	5.48 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	2.05 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

#### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)