

# YALB1852M14

by Burndy  
Catalog ID: YALB1852M14

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 185 mm, M14 Stud, 44.5 mm Spacing, Long Barrel, 52 mm Wire Strip Length



## Product Details

### General

|              |                      |
|--------------|----------------------|
| Die Index    | 18                   |
| Material     | Copper               |
| Plated       | Y                    |
| Plating Type | Tin - Electro Plated |
| Trade Name   | HYLUG™               |
| Type         | Metric Terminals     |
| UPC          | 781810639757         |
| UPC 12 Digit | 7818106397577        |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - B Length inch       | 2.00 in  |
| Dimension - Hole Size mm        | 15.1 mm  |
| Dimension - L Length Overall mm | 139.7 mm |
| Dimension - Length Overall inch | 5.50 in  |
| Dimension - Pad Width inch      | 1.29 in  |
| Dimension - Strip Length inch   | 2.05 in  |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | CM |

### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)