

YALB185F2M10

by Burndy
Catalog ID: YALB185F2M10

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 185 mm, M10 Stud, 44.5 mm Spacing, Long Barrel, 52 mm Wire Strip Length



Product Details

General

Die Index	18
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810642740
UPC 12 Digit	7818106427400

Dimensions

Dimension - B Length inch	2.12 in
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	137.4 mm
Dimension - Length Overall inch	5.41 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	2.05 in
Dimension - Z inch	0.42 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)