

## YALB185FM10

by Burndy  
Catalog ID: YALB185FM10

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 185 mm, M10 Stud, Long Barrel, 52 mm Wire Strip Length



## Product Details

### General

|              |                      |
|--------------|----------------------|
| Die Index    | 18                   |
| Material     | Copper               |
| Plated       | Y                    |
| Plating Type | Tin - Electro Plated |
| Trade Name   | HYLUG™               |
| Type         | Metric Terminals     |
| UPC          | 781810641842         |
| UPC 12 Digit | 7818106418422        |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length inch       | 2.12 in |
| Dimension - Hole Size mm        | 10.4 mm |
| Dimension - L Length Overall mm | 91.6 mm |
| Dimension - Length Overall inch | 3.61 in |
| Dimension - Pad Width inch      | 1.40 in |
| Dimension - Strip Length inch   | 2.05 in |
| Dimension - Z inch              | 0.42 in |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

### Certifications and Compliance

|                              |    |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

|                                    |
|------------------------------------|
| Standards - RoHS Compliance Status |
|------------------------------------|

|    |
|----|
| CM |
|----|

## Logistics

|                       |
|-----------------------|
| Minimum Pack Quantity |
|-----------------------|

|    |
|----|
| 10 |
|----|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)