

## YALB240M16

by Burndy  
Catalog ID: YALB240M16

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 240 mm, M16 Stud, Long Barrel



### Product Details

#### General

Die Index	20
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638941
UPC 12 Digit	7818106389411

#### Dimensions

Dimension - B Length inch	2.25 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	111.4 mm
Dimension - Length Overall inch	4.38 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	2.32 in
Dimension - Z inch	0.67 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

100
-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)