

YALB300F2M20

by Burndy
Catalog ID: YALB300F2M20

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 300 mm,
M20 Stud, 44.5 mm Spacing, Long Barrel, 73 mm Wire Strip Length



Product Details

General

| | |
|--------------|----------------------|
| Die Index | 22 |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Metric Terminals |
| UPC | 781810642894 |
| UPC 12 Digit | 7818106428944 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length inch | 2.81 in |
| Dimension - Hole Size mm | 23.8 mm |
| Dimension - L Length Overall mm | 184.5 mm |
| Dimension - Length Overall inch | 7.27 in |
| Dimension - Pad Width inch | 1.84 in |
| Dimension - Strip Length inch | 2.87 in |
| Dimension - Z inch | 0.89 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)