

YALB300M16

by Burndy
Catalog ID: YALB300M16

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 300 mm,
M16 Stud, Long Barrel



Product Details

General

Die Index	22
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638996
UPC 12 Digit	7818106389966

Dimensions

Dimension - B Length inch	2.69 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	124.4 mm
Dimension - Length Overall inch	4.90 in
Dimension - Pad Width inch	1.74 in
Dimension - Strip Length inch	2.76 in
Dimension - Z inch	0.67 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)