

## YALB400F2M20

by Burndy  
Catalog ID: YALB400F2M20

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 400 mm, M20 Stud, 44.5 mm Spacing, Long Barrel, 76 mm Wire Strip Length



### Product Details

#### General

Die Index	24
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810642931
UPC 12 Digit	7818106429311

#### Dimensions

Dimension - B Length inch	2.94 in
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	189.2 mm
Dimension - Length Overall inch	7.45 in
Dimension - Pad Width inch	1.98 in
Dimension - Strip Length inch	2.99 in
Dimension - Z inch	0.89 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)