

# YALB50M6

by Burndy  
Catalog ID: YALB50M6

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 50 mm, M6 Stud, Long Barrel



## Product Details

### General

Die Index	12
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638552
UPC 12 Digit	7818106385522

### Dimensions

Dimension - B Length inch	1.38 in
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	60.7 mm
Dimension - Length Overall inch	2.39 in
Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	1.46 in
Dimension - Z inch	0.33 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

20
----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)