

YALB6302M16

by Burndy
Catalog ID: YALB6302M16

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 630 mm, M16 Stud, 44.5 mm Spacing, Long Barrel, 83 mm Wire Strip Length



Product Details

General

Die Index	29
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639955
UPC 12 Digit	7818106399555

Dimensions

Dimension - B Length inch	3.19 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	190.4 mm
Dimension - Length Overall inch	7.50 in
Dimension - Pad Width inch	2.46 in
Dimension - Strip Length inch	3.27 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)