

## YALB630F2M12

by Burndy  
Catalog ID: YALB630F2M12

Cu Compression Metric Lug Terminal, 2 Holes, 630 mm, M12 Stud, Long Barrel



### Product Details

#### General

Die Index	31
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810643044
UPC 12 Digit	7818106430444

#### Dimensions

Dimension - B Length inch	3.19 in
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	186.9 mm
Dimension - Length Overall inch	7.36 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	3.27 in
Dimension - Z inch	0.55 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	2
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)