

## YALB70FM16

by Burndy  
Catalog ID: YALB70FM16

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 70 mm, M16 Stud, Long Barrel, 40 mm Wire Strip Length



### Product Details

#### General

Die Index	13
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Metric Terminals
UPC	781810641637
UPC 12 Digit	7818106416377

#### Dimensions

Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.32 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1.57 in
Dimension - Z inch	0.67 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

#### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

20
----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)