

# YALB952M14

by Burndy  
Catalog ID: YALB952M14

Cu Compression Metric Lug, 2 Hole, W/o Inspection Window, 95 mm, M14 Stud, 44.5 mm Spacing, Long Barrel, 40 mm Wire Strip Length



## Product Details

### General

Die Index	14
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810639573
UPC 12 Digit	7818106395733

### Dimensions

Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.86 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1.57 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

10
----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)