

YALB95FM8

by Burndy
Catalog ID: YALB95FM8

Cu Compression Metric Lug, 1 Hole, W/o Inspection Window, 95 mm, M8 Stud, Long Barrel, 40 mm Wire Strip Length



Product Details

General

| | |
|--------------|----------------------|
| Die Index | 14 |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Metric Terminals |
| UPC | 781810641644 |
| UPC 12 Digit | 7818106416444 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 1.50 in |
| Dimension - Hole Size mm | 8.4 mm |
| Dimension - L Length Overall mm | 68.9 mm |
| Dimension - Length Overall inch | 2.71 in |
| Dimension - Pad Width inch | 1.03 in |
| Dimension - Strip Length inch | 1.57 in |
| Dimension - Z inch | 0.36 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Certifications and Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

| |
|------------------------------------|
| Standards - RoHS Compliance Status |
|------------------------------------|

| |
|----|
| CM |
|----|

Logistics

| |
|-----------------------|
| Minimum Pack Quantity |
|-----------------------|

| |
|----|
| 10 |
|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)