

YAS1R2NTN

by Burndy
Catalog ID: YAS1R2NTN

Prop 65 Notice

Aluminum tubing stacking terminal-Straight lug, #2-#1 AWG Al,Cu, #2 AWG ACSR, .56 IN Stud, Red, .65 IN H, Tin plated



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	BG;243;K-5/8-1;CSA22
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810263211
UPC 12 Digit	7818102632111

Dimensions

Dimension - B Length inch	0.96 in
Dimension - D inch	3.43 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.85 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Pad Width inch	0.90 in
Dimension - Strip Length inch	1-3/32 in
Dimension - Z inch	1.05 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG
Conductor - AL Str Size	2 AWG;1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG
Conductor - Copper Str Size	2 AWG;1 AWG

Conductor - Copper Str Size Range	2 AWG-1 AWG
-----------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)