

# YAS25R2NTN

by Burndy  
Catalog ID: YAS25R2NTN

Prop 65 Notice

Aluminum tubing stacking terminal-Straight lug, 1/0 AWG Al,Cu,ACSR,  
.56 IN Stud, Yellow, .65 IN H, Tin plated



## Product Details

### General

Color Code	Yellow
Die Index	BG;243;K-5/8-1;CSA22
Feature - Barrel Style	Chamfered
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810246542
UPC 12 Digit	7818102465422

### Dimensions

Dimension - B Length inch	0.96 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.42 in
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	4.85 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.65 in
Dimension - P inch	1.29 in
Dimension - Pad Width inch	0.90 in
Dimension - Strip Length inch	1-3/32 in
Dimension - Z inch	1.05 in

### Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)