

YAS25R2N

by Burndy
Catalog ID: YAS25R2N

Prop 65 Notice

Straight Stacking Lug, Al Tubing, 2-NEMA Holes, 1/0 AWG Cu/Al, ACSR, Yellow, 0.56" Hole Dia.



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	BG;243;K-5/8-1;CSA22
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810050026
UPC 12 Digit	7818100500266

Dimensions

Dimension - B Length inch	0.96 in
Dimension - D inch	3.43 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.85 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Pad Width inch	0.90 in
Dimension - Strip Length inch	1-3/32 in
Dimension - Z inch	1.05 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)