

YAS26RN

by Burndy
Catalog ID: YAS26RN

Prop 65 Notice

Al Stackable compression Terminal- Straight Lug, 2/0 Al-Cu, 2/0 ACSR, 1 Hole, Gray



Product Details

General

Color Code	Gray
Connector Type	Terminal
Die Index	249;840;CSA24
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810104347
UPC 12 Digit	7818101043477

Dimensions

Dimension - B Length inch	1.47 in
Dimension - D inch	2.01 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	103 mm
Dimension - Length Overall inch	4.07 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.91 in
Dimension - Pad Width inch	1.24 in
Dimension - Strip Length inch	1-19/32 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	2/0 (6/1) Quail
Conductor - ACSR Str Size Range	2/0 (6/1) Quail
Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Conductor - Copper Str Size Range	2/0 AWG
-----------------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)