

YAS28R2N

by Burndy
Catalog ID: YAS28R2N

Prop 65 Notice

Aluminum Stacking Terminal - Straight lug, 4/0 AWG Al, Cu 4/0 AWG ACSR, Pink



Product Details

General

| | |
|--|---------------|
| Color Code | Pink |
| Connector Type | Terminal |
| Die Index | 249;840;CSA24 |
| Feature - Barrel Style | Tapered |
| Material | Aluminum |
| Physical Attribute - Number of Crimps Required | 1 |
| Physical Attribute - Number of Holes | 2 |
| Plated | N |
| Plating Type | Unplated |
| Trade Name | HYLUG™ |
| UPC | 781810050422 |
| UPC 12 Digit | 7818100504222 |

Dimensions

| | |
|-----------------------------------|------------|
| Dimension - B Length inch | 1.47 in |
| Dimension - D inch | 3.76 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - L Length Overall mm | 148 mm |
| Dimension - Length Overall inch | 5.83 in |
| Dimension - N inch | 0.63 in |
| Dimension - Outside Diameter inch | 0.91 in |
| Dimension - Pad Width inch | 1.24 in |
| Dimension - Strip Length inch | 1-19/32 in |
| Dimension - Z inch | 1.38 in |
| Physical Attribute - Tongue Angle | Straight |

Conductor Related

| | |
|---------------------------------|-----------------------|
| Conductor - ACSR Str Size | 4/0 (6/1) Penquin AWG |
| Conductor - ACSR Str Size Range | 4/0 (6/1) Penquin AWG |
| Conductor - AL Str Size | 4/0 AWG |
| Conductor - AL Str Size Range | 4/0 AWG |

| | |
|-----------------------------------|---------|
| Conductor - Copper Str Size | 4/0 AWG |
| Conductor - Copper Str Size Range | 4/0 AWG |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)