

# YAS33R2N

by Burndy  
Catalog ID: YAS33R2N

Prop 65 Notice

Straight Stacking Lug, Al Tubing, 2-NEMA Holes, 400 kcmil Cu/Al, 397 kcmil ACSR, Green, 0.56" Hole Dia.



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	317;705
Material	Aluminum
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810051795
UPC 12 Digit	7818100517955

### Dimensions

Dimension - B Length inch	2.3 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	182 mm
Dimension - Length Overall inch	7.18 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.68 in
Dimension - Strip Length inch	2 in
Dimension - Z inch	1.82 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size	400 kcmil
Conductor - AL Str Size Range	400 kcmil
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)