

YASO33R2N

by Burndy
Catalog ID: YASO33R2N

Prop 65 Notice

Aluminum Stacking terminal - Stacking lug, 400 Kcmil Al, 397 Kcmil Cu ACSR, Green



Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	317;705
Material	Aluminum
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810053379
UPC 12 Digit	7818100533799

Dimensions

Dimension - B Length inch	2.3 in
Dimension - Height fraction	9/10 in
Dimension - Height inch	0.9 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	182 mm
Dimension - Length Overall inch	7.18 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.68 in
Dimension - Strip Length inch	2 in
Dimension - Z inch	0.72 in

Physical Attribute - Tongue Angle	Offset
-----------------------------------	--------

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size	400 kcmil
Conductor - AL Str Size Range	400 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)