

YASO4R2N

by Burndy
Catalog ID: YASO4R2N

Prop 65 Notice

Stacking Lug, Al Tubing, 2-NEMA Holes, #4 -#3 AWG Cu/Al,ACSR,
Orange, 0.56" Hole Dia.



Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	BG;K-5/8-1;243
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810053447
UPC 12 Digit	7818100534477

Dimensions

Dimension - B Length inch	0.96 in
Dimension - D inch	3.02 in
Dimension - Height fraction	1-1/5 in
Dimension - Height inch	1.21 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.85 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Pad Width inch	0.90 in

Dimension - Strip Length inch	1-3/32 in
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Offset

Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan
Conductor - ACSR Str Size Range	4 (6/1) Swan
Conductor - AL Str Size	4;3
Conductor - AL Str Size Range	4-3
Conductor - Copper Str Size	4;3
Conductor - Copper Str Size Range	4-3

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)