

YAV0252M5

by Burndy
Catalog ID: YAV0252M5

Hylug Copper tubing Compression terminals, 1.5-2.5 mm², M5 Stud, 2 Holes, Tin Plated



Product Details

General

Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637562
UPC 12 Digit	7818106375622

Dimensions

Dimension - B Length inch	0.27 in
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	44.7 mm
Dimension - Length Overall inch	1.76 in
Dimension - Pad Width inch	7.9 in
Dimension - Strip Length inch	0.28 in
Dimension - Z inch	0.24 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)