

YAV0252M8

by Burndy
Catalog ID: YAV0252M8

Hylug Copper tubing Compression terminals, 25 mm², M8 Stud, 2 Holes, Tin Plated



Product Details

General

Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637685
UPC 12 Digit	7818106376855

Dimensions

Dimension - B Length inch	0.27 in
Dimension - Hole Size mm	8.4 mm
Dimension - L Length Overall mm	49.8 mm
Dimension - Length Overall inch	1.96 in
Dimension - Pad Width inch	11.0 in
Dimension - Strip Length inch	0.28 in
Dimension - Z inch	0.32 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)