

YAV025M5

by Burndy
Catalog ID: YAV025M5

Copper Tubing Terminal, 1 Hole W/insp window, 2.5 mm Class 2,5, 5 mm Stud



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810235256
UPC 12 Digit	7818102352566

Dimensions

Dimension - B Length inch	0.27 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	19.1 mm
Dimension - Length Overall inch	0.75 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.15 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	0.28 in
Dimension - Z inch	0.24 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)