

YAV062M5

by Burndy
Catalog ID: YAV062M5

Hylug Copper tubing Compression terminals,4-6mm²,M5 Stud, 2 Holes,Tin Plated



Product Details

General

Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637708
UPC 12 Digit	7818106377088

Dimensions

Dimension - B Length inch	0.41 in
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	49.5 mm
Dimension - Length Overall inch	1.95 in
Dimension - Pad Width inch	9.5 in
Dimension - Strip Length inch	0.43 in
Dimension - Z inch	0.26 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)