

# YAV062M8

by Burndy  
Catalog ID: YAV062M8

Hylug Copper tubing Compression terminals, 4-6mm<sup>2</sup>, M8 Stud, 2 Holes, Tin Plated



## Product Details

### General

Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637722
UPC 12 Digit	7818106377222

### Dimensions

Dimension - B Length inch	0.41 in
Dimension - Hole Size mm	8.4 mm
Dimension - L Length Overall mm	54.4 mm
Dimension - Length Overall inch	2.14 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	0.43 in
Dimension - Z inch	0.34 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity

100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)