

## YAV102M8

by Burndy  
Catalog ID: YAV102M8

HYLUG™ Copper tubing Compression terminals, 10 mm, M8 Stud, 2 Holes, Tin Plated



### Product Details

#### General

Die Index	49
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637579
UPC 12 Digit	7818106375799

#### Dimensions

Dimension - B Length inch	11.2 in
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.14 in
Dimension - Pad Width inch	13.2 in
Dimension - Strip Length inch	0.43 in
Dimension - Z inch	0.36 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)