

# YAV120F2M20

by Burndy  
Catalog ID: YAV120F2M20

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 120 mm, M20 Stud, 44.5 mm Spacing, Standard Barrel, 27 mm Wire Strip Length



## Product Details

### General

Die Index	15
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Metric Terminals
UPC	781810640869
UPC 12 Digit	7818106408699

### Dimensions

Dimension - B Length inch	1.03 in
Dimension - L Length Overall mm	130 mm
Dimension - Length Overall inch	5.12 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1.06 in
Dimension - Z inch	0.89 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	10
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)