

YAV120M8

by Burndy
Catalog ID: YAV120M8

Copper Tubing Terminal, 1 Hole W/insp window, 120 mm Class 2, 15 Index,
8 mm Stud



Product Details

General

Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322017
UPC 12 Digit	7818103220177

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	0.03 in
Dimension - Bolt Hole Size inch	0.17 in
Dimension - Bolt Size fraction	#8
Dimension - D inch	0.74 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - Inside Diameter inch	0.59 in
Dimension - L Length Overall mm	4 mm
Dimension - Length Overall inch	0.15 in
Dimension - N inch	0.37 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	0.14 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size inch	#8

Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	10

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)