

YAV1502M12

by Burndy
Catalog ID: YAV1502M12

Non Insul Cu Comp Tubular Terminal, Metric, 2 Hole/W/InspWindow, 150 mm, M12 Stud, Tin-Electro Plated, 17 Index



Product Details

General

| | |
|--------------------------------------|----------------------|
| Connector Type | Terminal |
| Die Index | 17 |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| Type | Metric Terminals |
| UPC | 781810442739 |
| UPC 12 Digit | 7818104427399 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-3/50 in |
| Dimension - B Length inch | 26.2 in |
| Dimension - D inch | 2.66 in |
| Dimension - Hole Size inch | 0.53 in |
| Dimension - Hole Size mm | 13 mm |
| Dimension - L Length Overall mm | 113 mm |
| Dimension - Length Overall inch | 4.45 in |
| Dimension - N inch | 0.53 in |
| Dimension - Outside Diameter inch | 0.88 in |
| Dimension - Pad Width inch | 30.5 in |
| Dimension - Strip Length inch | 1.06 in |
| Dimension - Z inch | 0.55 in |

| | |
|-----------------------------------|----------|
| Physical Attribute - Tongue Angle | Straight |
|-----------------------------------|----------|

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|---------------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Size | 300 |
| Conductor - Copper Str Size Range | 300 |
| Conductor Type | CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)