

# YAV150FM16

by Burndy  
Catalog ID: YAV150FM16

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 150 mm, 16 mm Stud, 3.00 IN L, Compression, 17 Index, 29 mm Strip Length



## Product Details

### General

Connector Type	Terminal
Die Index	17
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322055
UPC 12 Digit	7818103220555

### Dimensions

Dimension - B Length inch	1.06 in
Dimension - Hole Size inch	0.67 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1.14 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)