

YAV150M12

by Burndy
Catalog ID: YAV150M12

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W,
150mmClass2, 1/2" stud, Tin - Electro Plated



Product Details

General

Connector Type	Terminal
Die Index	17
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810285725
UPC 12 Digit	7818102857255

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.53 in
Dimension - Bolt Size fraction	#12
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	68.3 mm
Dimension - Length Overall inch	2.69 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.2 in
Dimension - Strip Length inch	1.06 in
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300
Conductor - Copper Str Size Range	300
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	10

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)